LUMO LEAD FITTING INSTRUCTIONS

Sliding lead fitting



Loosen the cap, but do not remove. Slide the line through the lead ensuring the hook sits at the opposite end to the cap.



Slide the lead all the way down to the hook. If possible the bottom of the lead should sit over the hook eye.



Tighten the cap firmly by hand so that it grips the line.

TECHNICAL SPECIFICATIONS

Dimensions	73mm x 15mm x 15mm
Weight	45 or 60 grams
Depth rating	> 5000 meters
Light	Glows for up to six hours
Ease of use	Easy to attach and locks to line with a patented collet line grip
Effectiveness	No reduction in target catch
Housing	Lead encapsulated in a durable, luminescent nylon sheath

Safety and correct use of the lumo sliding lead



Ensure the correct orientation of the Lumo Sliding Lead



There should be no crimps or other obstructions fitted to the line between the lead and the hook fitting, as this will prevent the lead from safely sliding down the branch line in the event of a bite off.



Check each lead after use and push them back down to the hook if necessary $\footnote{\footnote{100}}$



Sliding Lumo Leads should not be placed at a distance greater than 5cm from the hook on vessels using a bait caster.

Lumolead model variations

LUMOLEAD - 45G

Colour Options	Luminescent (glows for 6 hours)
	Black (doesn't glow)
	Natural (doesn't glow)

LUMOLEAD - 60G

Colour Options	Luminescent (glows for 6 hours)
	Black (doesn't glow)
	Natural (doesn't glow)

